

Product Information

APX 100 (New Emulsion)

ISO 100 photo-film for black and white prints

Introduction

AgfaPhoto APX 100 is a medium speed black and white photo camera Film suitable for a broad variety of indoor and outdoor applications of photography where good lighting exists.

APX 100 is capable of generating high quality images with fine grain and good sharpness. In addition it is a good choice in case enlargements are needed.

Available Format

APX 100 Film is available in 35mm format with 36 exposures only.

Features

- ✓ Mid speed film, rated at ISO 100/21°
- ✓ Suitable for a wide range of general indoor and outdoor photography applications
- ✓ Fine grain
- ✓ Good sharpness
- ✓ Broad tonal range with good contrast.
- ✓ Broad exposure latitude.
- ✓ Compatible with a good variety of developers.

Storage

We advise unprocessed films to be stored in a cool dry place - and when possible (prior to and after exposure) in its original packaging. Advisable temperatures between 10-20°C / 50-68°F.

We advise storing processed negatives in a cool dry place in the dark, and in suitable sleeves. Advised temperatures of between 10-20°C / 50-68°F.

Exposure

APX 100 has a speed rating of ISO 100 / 21° (100ASA, 21DIN) to daylight. Although it is possible to rate the film at 50/18° and 200/24°, the film performs at its optimum when rated at ISO 100 .

When rated at any other suggested ISO ratings, quality does diminish in terms of grain and sharpness. If alternative speed settings to ISO 100 are to be used, it is advisable that tests with adapted times will be carried out first to ensure that these alternative speeds are suitable.

Once a film is exposed, we advise to have it processed as

soon as practical. However, images on exposed but unprocessed films will not degrade for several months provided they are stored as we advise in cool and dry conditions.

Filter Factors

APX 100 can be used with all standard types of filters (colour, polarising and neutral density filters). It is advised that the filter manufacturer's instructions are followed in terms of any exposure compensation factors needed.

Processing / Agitation

APX 100 Film is suitable for processing in most types of processing equipment – including spiral tanks, rotary processors, dishes/trays, deep tanks and automatic processors.

A wide range of developers are suitable for use. A variety of Developer choices and their guide process times / temperatures and dilutions are shown in the table below.

Development Times

The table below gives our advised 'guide' times for both manual and machine processing AgfaPhoto APX 100 Film.

These times are deemed appropriate for generating negatives of average contrast, and enable good printing in most enlargers.

Since they are intended as a 'guide' only, they may require slight adjustments to enable them to closer match what a user requires.

All quoted 'guide' times are based on intermittent agitation in standard tanks at 20° (first minute with permanent agitation, afterwards agitate every 30 seconds). If continuous agitation is to be given, we advise reducing these times by up to 15%. Also, for rotary processors (without a pre-rinse), it is likely that these times need to be reduced by up to 15%. Note, we do not advise pre-rinsing – as it can lead to uneven processing. specifications may occur without prior notice.

Developer		Dilution	Development Times (Minutes)	Notes
ADOX	Adonal (Rodinal)	1 + 25	5:30	Recommended: EI 80/20° Recommended: EI 160/23°
		1 + 50	10:00	
	Atomal	Stock	9:30	
		1 + 2	22:00	
ILFORD	ID-11	Stock	9:00	
		1 + 1	11:30	
		1 + 3	21:00	
	Microphen	Stock	8:30	
		1 + 1	10:30	
		1 + 3	14:30	
	Perceptol	Stock	12:30	
		1 + 1	15:30	
	KODAK	D-76	Stock	
1 + 1			11:30	
1 + 3			21:00	
SPUR	HRX	1 + 20	10:00	Recommended: EI 64/20°
	ACUROL-N	1 + 70	11:00	Recommended: EI 100/20°
	UFP	1 + 30	8:00	Recommended: EI 80/20°

Notice: The data herein published were derived from materials taken from general production runs. However, changes in specifications may occur without prior notice.

AgfaPhoto is used under license of Agfa-Gevaert NV & Co. KG or Agfa-Gevaert NV. Neither Agfa-Gevaert NV & Co KG nor Agfa-Gevaert NV manufacture this product or provide any product warranty or support. For service, support and warranty information, contact the distributor or manufacturer.
AgfaPhoto Holding GmbH - www.agfaphoto.com
Produced for and distributed by Lupus Imaging & Media GmbH
Co. KG · D-40764 Langenfeld · Leichlinger Str. 14
info@lupus-im.com · www.lupus-imaging-media.com