

Bergger Pancro400 - 22 °C

Bergger Pancro400 à EI 400/27°

ADOX	Adotech II 1+14	Adonal 1+25	Adonal 1+50	Adonal 1+100	Adotech III 1+9	Adotech III 1+11	ADX-II 1+17	ADX-II 1+24	Atomal 49 pur	Atomal 49 1+1	Atomal 49 1+2
22 °C		06.45	19.00								
AGFA	Refinal	Rodinal 1+25	Rodinal 1+50	Rodinal 1+100	R09 special 1+15	R09 special 1+31	Studional 1+15	Studional 1+31	Atomal pur	Atomal 1+1	Atomal 1+2
22 °C		06.45	19.00				cf 20 °C				
ARS- IMAGO	FD 1+19	FD 1+39	FD 1+59								
22 °C		09.00									
BERGGER	BerSpeed pur	BerSpeed 1+1		PMK 1+2+100		BER49 pur	BER49 1+1				
22 °C		10.15		15.15		11.45	20.00				
FOMA		R09 New 1+25	R09 New 1+50	R09 New 1+100		Foma LQN 1+10	Foma LQR 1+10	Universal 1+3	Foma Excel pur	Foma Excel 1+1	Fomadon P pur
22 °C		06.45	19.00								
ILFORD	ID-11 pur	ID-11 1+1	ID-11 1+3	Microphen pur	Microphen 1+1	Microphen 1+3	Perceptol pur	Perceptol 1+1	Perceptol 1+3	Ilfotec LC29 1+9	Ilfotec LC29 1+19
22 °C	07.40	14.30									
KODAK	D-76 pur	D-76 1+1	D-76 1+3	TMAX-dev 1+4	TMAX-dev 1+7	TMAX-dev 1+9	Microdol-X	Microdol-X 1+1	Microdol-X 1+3	HC-110 (A) 1+15	HC-110 (B) 1+31
22 °C	07.40	14.30									07.40
(suite)	XTOL	XTOL 1+1	XTOL 1+2	XTOL 1+3	DK-50 1+1	D-19	D-96				
22 °C	08.30	15.15									
ROLLEI	RHS 1+7	RHS 1+9	RHS 1+15	RLS 1+4	RPX-D 1+5	RPX-D 1+11	Supergrain 1+9	Supergrain 1+12	Supergrain 1+15		
22 °C							08.00				

Bergger Pancro400 à EI 800/30°

BERGGER	BerSpeed pur	BerSpeed 1+1		PMK 1+2+100		BER49 pur	BER49 1+1				
22 °C		cf 24 °C									

Bergger Pancro400 à EI 1600/33°

BERGGER	BerSpeed pur	BerSpeed 1+1		PMK 1+2+100		BER49 pur	BER49 1+1				
22 °C		cf 24 °C									